

## Submersible Flat-Surface, Self-Cleaning pH and ORP Electrodes



Quick disconnect design saves time and money

Installs in seconds, no tools necessary

Flat surface design resists coating

**CPVC or PVDF models available** 

Available with or without ATC elements

The submersion pH and ORP electrodes from Sensorex are designed for measurements in tanks, flumes and sewer lines. Submersion designs are also well suited for high suspended solids applications, flocculation operations which require low velocities, or in tanks with high agitation.

Where low velocities are present and coating is a problem, the electrode can be mounted at a 45 degree angle facing into the flow so as to obtain increased scrubbing action across the measuring surface.

The cartridge quick disconnect design makes changing electrodes a snap and minimizes down time due to electrode maintenance.

Model S651CD offers a pH glass protection feature and the extra performance of acrylamide reference gel.

#### **Specifications**

0-14pH (0-12pH without Na+ error)

**Wetted Materials** 

Body/Junction: CPVC/HDPE ("-CD" models)

PVDF/ Porous PVDF ("-KD" models)

+/- 2000mV for ORP

Measuring Surface: pH glass (pH), Platinum or Gold (ORP)

O-rings: Viton Gasket: **EPR** 

**Temperature/Pressure Range** 

(all models ending in "-CD") = 0C\* - 75C (0-100psig), 80C (0-85psig)

(all models ending in "-KD") =  $0C^*$  - 100C (0-100psig)

Note: From 0 to 10C, electrodes will exhibit slower response time.

**Reference Type** Ag/AgCl, Sealed Double Junction

Parts covered by this product data sheet include:

S650CD, S650CD-ORP, S650KD, S650KD-ORP, S650CD-LC, S650KD-HT, S651CD, S651CD-ORP, S650CD-LC

iSweek www.isweek.com

Add: 16/F, Bldg. #3, Zhongke Mansion, No.1 Hi-Tech S. Rd, Hi-Tech Park South, Shenzhen, Guangdong, 518067 P.R.China

Tel: +86-755-83289036 Fax: +86-755-83289052

E-mail: sales@isweek.com





## **CPVC Electrodes**


pH - S650CD, S650CD-HT, S650CD-LC

ORP - S650CD-ORP, S650CD-ORP-HT, S650CD-ORP-LC, S650CD-AU

pH & ORP - S651CD, S651CD-ORP











### **CPVC CABLES WITHOUT ATC - S653**

#### **CPVC CABLES WITH ATC - S653TC**









**iSweek** www.isweek.com

Add: 16/F, Bldg. #3, Zhongke Mansion, No.1 Hi-Tech S. Rd, Hi-Tech Park South, Shenzhen, Guangdong, 518067 P.R.China

Tel: +86-755-83289036


Fax: +86-755-83289052

E-mail: sales@isweek.com




# **PVDF Electrodes**


pH - S650KD, S650KD-HT, S650KD-LC




PVDF CABLE WITHOUT ATC -S653K



ORP - S650KD-ORP, S650KD-ORP-HT, S650KD-ORP-LC



PVDF CABLE WITH ATC - S653TK



ISweek www.isweek.com

Add: 16/F, Bldg. #3, Zhongke Mansion, No.1 Hi-Tech S. Rd, Hi-Tech Park South, Shenzhen, Guangdong, 518067 P.R.China



### **ORDERING INFORMATION**


#### Systems without temperature compensation

ORDER 2 ITEMS	DESCRIPTION	CPVC PARTS	PVDF PARTS
1. Select one electrode(pH or ORP)	pH combination electrode pH combination electrode( high temp) pH comb electrode w/protective tip Model for Low Ionic samples Model for acidic HF samples ORP combination electrode ORP combination electrode (high temp) ORP combination electrode (Gold tip)	\$650CD \$651CD \$651CD \$650CD-LC \$650CD-HF \$650CD-ORP \$651CD-ORP \$650CD-ORP-AU	S650KD S650KD-HT N/A S650KD-LC S650KD-HF S650KD-ORP S650KD-ORP-HT S650KD-ORP-AU
2. Select one cable assembly	For conduit use	S653-"cable length"-"Connector"	S653K-"cable length"-"Connector"


#### Systems with temperature compensation

ORDER 2 ITEMS	DESCRIPTION	CPVC PARTS	PVDF PARTS
1. Select one electrode	pH combination electrode pH combination electrode( high temp) Model for Low Ionic samples Model for acidic HF samples pH comb electrode w/protective tip	S650CD S651CD S650CD-LC S650CD-HF S651CD	S650KD S650KD-HT S650KD-LC S650KD-HF N/A
2. Select one cable assembly	For conduit use for exposed cable use	S653TC -"ATC CODE"-cable length"-"Connectors"	S653TK-"ATC CODE"-"cable length"-"Connectors"


#### **SELF-CLEANING OPERATION**



#### **ABRASION-FREE OPERATION**



#### **VISCOUS MATERIAL OPERATION**



**İSweek** www.isweek.com

Add: 16/F, Bldg. #3, Zhongke Mansion, No.1 Hi-Tech S. Rd, Hi-Tech Park South, Shenzhen, Guangdong, 518067 P.R.China

Tel: + 86-755-83289036 Fa

Fax: +86-755-83289052

E-mail: sales@isweek.com